













3M™ E-A-Rfit™ Dual-Ear Validation System












Disposable FoamTest Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-Rsoft™ Yellow Neons™ (regular-sized)	393-2000-50 	<ul style="list-style-type: none"> E-A-Rsoft™ Yellow Neons™ E-A-Rsoft™ Yellow Neon™ Blasts™ E-A-Rsoft™ SuperFit™ Tattoo™ Nitro™ 	310-1250, Yellow Neons™ Uncorded in Pillow Pak Regular Size 311-1250, Yellow Neons™ Corded in Poly Bag, Regular Size 311-1252, Yellow Neon™ Blasts™ Corded in Poly Bag, Regular Size 311-1254, SuperFit™ Corded in Poly Bag, Regular Size 311-1256, Yellow Neons™ Corded in Poly Bag, Regular Size 311-1257, Yellow Neon™ Blasts™ Corded in Poly Bag, Regular Size 311-4106, Metal Detectable Corded in Poly Bag, Regular Size 311-4109, SuperFit™ Metal Detectable Corded in Poly Bag, Reg Size 311-4110, E-A-Rsoft™ Metal Detectable AV Corded, Poly Bag, Reg Size 312-1250, Yellow Neons™ Uncorded Earplugs in Poly Bag, Reg Size 312-1252, Yellow Neon™ Blasts™ Uncorded in Poly Bag, Reg Size 312-1256, SuperFit™ Uncorded Earplugs in Poly Bag, Reg Size 391-1004, Yellow Neons™ One Touch™ Refill Reg Size 391-1010, Yellow Neon™ Blasts™ One Touch™ Dispens. Refill Reg Size 391-1254, SuperFit™ One Touch™ Refill Regular Size P1000, Nitro™ Earplugs Uncorded P1001, Nitro™ Earplugs Corded P1100, Nitro™ Tattoo™ Earplug Uncorded P1101, Nitro™ Tattoo™ Earplug Corded
E-A-Rsoft™ Yellow Neons Large	393-2014-50 	<ul style="list-style-type: none"> E-A-Rsoft™ Yellow Neons Large 	311-1251, E-A-Rsoft™ Yellow Neons™ Large Corded in Poly bag 312-1251, E-A-Rsoft™ Yellow Neons™ Large Uncorded in Poly bag 312-1255, E-A-Rsoft™ SuperFit™ Large, Uncorded 391-1005, E-A-Rsoft™ Yellow Neons™ Large Uncorded Dispens. Refill
E-A-R™ Classic™	393-2003-50 	<ul style="list-style-type: none"> E-A-R™ Classic™ 	310-1001, Uncorded Earplugs in Pillow Pak 310-1060, Uncorded in Pillow Pak 310-1080, Corded Earplugs in Poly Bag 311-1081, Corded Earplugs in Econopack Dispenser Box 311-1101, Corded Earplugs in Poly Bag 312-1080, Uncorded Earplugs in Econopack 312-1082, Uncorded Earplugs in Econopack 312-1201, Uncorded Earplugs in Poly Bag 390-1000, Uncorded Earplugs in Value Pak 391-1001, One Touch™ Refill VP311-1101, Corded Earplugs in 5 PR-100 Pak
E-A-R™ Classic™ Small	393-2007-50 	<ul style="list-style-type: none"> Classic™ Small 	310-1103, Uncorded Earplugs in Pillow Pak 311-1106, Corded Earplugs in Poly Bag 310-4003, Platinum™ Uncorded Earplugs, Poly Bag, 310-1009, SuperFit™ 30 Uncorded Earplugs, in Pillow Pak 312-4201, SuperFit™ 30 Uncorded Earplugs in Poly Bag 311-1126, SuperFit™ 30 Corded Earplugs in Poly Bag 391-1002, SuperFit™ 30 One Touch™ Refill
E-A-R™ Classic™ Plus	393-2009-50 	<ul style="list-style-type: none"> Classic™ Plus 	310-1101, Uncorded Earplugs in Pillow Pak 311-1105, Corded Earplugs in Poly Bag 311-4101, Metal-Detectable Corded Earplugs in Poly Bag 310-1008, SuperFit™ 33 Uncorded Earplugs in Pillow Pak 311-1125, SuperFit™ 33 Corded Earplugs in Poly Bag SF-01-003, SuperFit 36
E-A-R™ Classic™ Soft	Not Available	<ul style="list-style-type: none"> Classic™ Soft 	311-6000 and 311-6001
E-A-R™ TaperFit™ 2	393-2006-50 	<ul style="list-style-type: none"> TaperFit™ 2 	312-1219, Uncorded, Poly Bag, Reg. 312-1223, Corded, Poly Bag, Reg.
E-A-R™ TaperFit™ 2 Large	393-2027-50 	<ul style="list-style-type: none"> TaperFit™ 2 Large 	312-1221, TaperFit™ 2 Earplugs, Uncorded 312-1224, TaperFit™ 2 Earplugs, Corded,









Disposable FoamTest Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-Rsoft™ FX™	393-2004-50 	<ul style="list-style-type: none"> E-A-Rsoft™ FX™ 	312-1260, Corded Earplugs in Poly Bag 2000 PR/Case 312-1261, Uncorded Earplugs in Poly Bag 2000 PR/Case 312-1274, Corded Earplugs in Poly Bag 1000 PR/Case
E-A-R™ E-Z-fit™	393-2005-50 	<ul style="list-style-type: none"> E-A-R™ E-Z-Fit™ 	312-1208, Uncorded Earplugs in Poly Bag 2000 PR/Case 312-1222, Corded Earplugs in Poly Bag 2000 PR/Case
E-A-Rsoft™ Grippers	393-2021-50 	<ul style="list-style-type: none"> E-A-Rsoft™ Grip-pers 	312-6001, E-A-Rsoft™ Grippers Corded Earplugs, in Polybag
1100	393-2010-50 	<ul style="list-style-type: none"> 3M™ 1100 3M™ 1110 	1100, Uncorded Foam Earplugs in Poly Bag 1000 PR/Case 1110, Corded Foam Earplugs in Poly Bag 500 PR/Case

Push-to-Fit Probed Test Plugs


Push-to-Fit ProbedTest Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-R™ Push-Ins™	393-2002-50 	<ul style="list-style-type: none"> Push-Ins™ 	318-1000, Uncorded Earplugs in Poly Bag 318-1001, Corded Earplugs in Poly Bag 318-1002, Uncorded Earplugs in Poly Bag 318-1003, Corded Earplugs in Poly Bag 318-1004, Uncorded Earplugs in Poly Bag 318-1005, Corded Earplugs in Poly Bag 318-3000, Metal Detectable
E-A-R™ Skull Screws™	393-2012-50 	<ul style="list-style-type: none"> Skull Screws™ 	P1300, Uncorded Earplugs in Poly Bag P1301, Corded Earplugs in Poly Bag
Push-Ins™ with Grip Rings	393-2015-50 	<ul style="list-style-type: none"> Push-Ins™ with Grip Rings 	318-1009, Push-Ins™ with Grip Rings Corded in Poly bag 318-1008, E-A-R™ Push-Ins™ with Grip Rings Uncorded, Poly bag
No Touch™ Probed	393-2013-50 	<ul style="list-style-type: none"> No Touch™ 	P2000, Uncorded in Poly Bag P2001, Corded in Poly Bag
E-A-R™ Express™ Pod Plugs™	393-2008-50 	<ul style="list-style-type: none"> Express™ PodPlugs™ 	321-2100, Blue Grips in Pillow Pak 321-2200, Assorted Color Grips in Pillow Pak 311-1114, Corded Blue Grips in Pillow Pak 311-1115, Corded Assorted Grips in Pillow Pak 311-1127, Corded Metal-Detectable Earplugs in Pillow Pak
E-A-R™ Flexible Fit HA Earplugs	393-2026-50 	<ul style="list-style-type: none"> Flexible Fit 	328-1000, E-A-R™ Flexible Fit HA Uncorded in Polybag 328-1001, E-A-R™ Flexible Fit HA Corded in Polybag
Push-Ins™ SofTouch™	Not available		318-4000, 318-4001, E-A-R™ Push-Ins™ SofTouch™
Pistonz™	Not available		P1400, P1401, P1401A, Pistonz™
UltraFit™ 27	Not available		340-8001, 340-8002


Reusable Probed Test Plugs

Reusable Probed Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
E-A-R™ UltraFit™ Probed	393-2001-50 	<ul style="list-style-type: none"> E-A-R™ UltraFit™ E-A-R™ Tracer™ 	340-4001, Uncorded Earplugs in Carrying Case 340-4002, Corded Earplugs in Carrying Case 340-4003, Uncorded Earplugs in Poly Bag 340-4004, Corded Earplugs in Poly Bag 340-4007, Metal Detectable Corded Earplugs in Poly Bag 340-4014, Corded Earplugs in Econopack 340-4036, with Cotton Cord in Poly Bag 340-4044, with Cloth Cord in Paper Envelope 340-4017, Metal Detectable Corded Earplugs in Econopack TR-01-000, Tracer™ Metal Detectable Corded Earplugs VP340-4004, Corded Earplugs in 5 PR-100 Pak UF-01-012, UltraFit 20 UF-01-015, UltraFit 14
Tri-Flange™ Probed	393-2011-50 	<ul style="list-style-type: none"> Tri-Flange™ E-A-R™ UltraFitPlus™ 	P3000, Vinyl Corded Earplugs in Poly Bag P3001, Cloth Corded Earplugs in Poly Bag 340-6004, UltraFit Plus™ Corded Earplugs in Poly Bag 340-6002, UltraFit Plus™ Corded Earplugs in Carrying Case
Reusable 1260	393-2016-50 	<ul style="list-style-type: none"> 1260 	1260, Reusable Earplugs, uncorded 1270, Reusable Earplugs, corded 1271, Reusable Earplugs, corded with carry case
UltraFit™ Silicone & Pump Plus	393-2017-50 	<ul style="list-style-type: none"> UltraFit™ Silicone 	Pump Plus 340-3002, 3M™ UltraFit™ Silicone Corded Earplugs, One Size
Pump Millennium Small	393-2023S-50 	<ul style="list-style-type: none"> Pump Millennium 	3M™ Pump Millennium Small
Pump Millennium Med	393-2023M-50 	<ul style="list-style-type: none"> Pump Millennium 	3M™ Pump Millennium Medium Not available: 1241 Reusable Earplugs
Pump Millennium Lg	393-2023L-50 	<ul style="list-style-type: none"> Pump Millennium 	3M™ Pump Millennium Large
Reusable 1290	393-2024-50 	<ul style="list-style-type: none"> Reusable 1290 	3M™ Reusable 1290, 1291, 1292, 1293
TEP/LEP/EEP	393-2030-50 	<ul style="list-style-type: none"> Skull Screws/ Torque™ (regular and metal detectable) 	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2031-50 	<ul style="list-style-type: none"> CCC-GRM-25 	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2032-50 	<ul style="list-style-type: none"> UltraFit™ Small 	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR

Reusable Probed Test Plugs	Probed Test Plug SKU	Brand Names	Crossover Product SKUs and Descriptions
TEP/LEP/EEP	393-2033-50 	<ul style="list-style-type: none"> UltraFit™ MED 	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
	393-2034-50 	<ul style="list-style-type: none"> UltraFit™ Large 	The following products fitted with this tip: TEP-100/200, LEP-100/200, LEP-200 OR, EEP-100, EEP-100 OR
Combat Arms™ 4.0 – SMALL	393-2018S-50 	<ul style="list-style-type: none"> Combat Arms™ 	370-1030, 3M™ Combat Arms™ Single Tip Corded Earplugs Small
Combat Arms™ 4.0 – MED	393-2018M-50 	<ul style="list-style-type: none"> Combat Arms™ 	370-1031, 3M™ Combat Arms™ Single Tip Corded Earplugs Medium
Combat Arms™ 4.0 – LARGE	393-2018L-50 	<ul style="list-style-type: none"> Combat Arms™ 	370-1032, 3M™ Combat Arms™ Single Tip Corded Earplugs Large
Combat Arms™ 4.1 – SMALL	393-2022S-50 	<ul style="list-style-type: none"> Combat Arms™ 	370-1040, 3M™ Combat Arms™ 4.1 Hear-Through Earplugs, 28 dB, Single Ended, Small
Combat Arms™ 4.1 – MED	393-2022M-50 	<ul style="list-style-type: none"> Combat Arms™ 	370-1041, 3M™ Combat Arms™ 4.1 Hear-Through Earplugs, 28 dB, Single Ended, Medium
Combat Arms™ 4.1 – LARGE	393-2022L-50 	<ul style="list-style-type: none"> Combat Arms™ 	370-1042, 3M™ Combat Arms™ 4.1 Hear-Through Earplugs, 28 dB, Single Ended, Large



Probed Test Cushions

Probed Test Cushions	Probed Test Cushion SKU	Brand Names	Crossover Product SKUs and Descriptions
PELTOR™ Earmuff Test Cushion A 	393-3004-2	Earmuffs: <ul style="list-style-type: none"> Optime™ 105 Optime™ III 	H10A & AHV, 3M™ PELTOR™ Optime™ 105, Over-the-head H10P3E, 3M™ PELTOR™ Optime™ 105, Hard Hat Attached H10B, PELTOR™ Optime 105 Neckband H540A & AHV, PELTOR™ Optime III Over-the-head (Bulls Eye III)H540B, PELTOR™ Optime III Neckband H540P3E & P3GS, PELTOR™ Optime III Hard Hat Attached


Probed Test Cushions	Probed Test Cushion SKU	Brand Names	Crossover Product SKUs and Descriptions
<p>PELTOR™ Earmuffs X1/X2 Test Cushions B</p>	<p>393-3001-2</p> 	<p>Earmuffs:</p> <ul style="list-style-type: none"> • X1, X2 • Optime™ 95 • Optime™ 98 • Optime™ 101 • Optime™ I • Optime™ II • M Series Respirator Headgear <p>Headsets:</p> <ul style="list-style-type: none"> • LiteCom • LiteCom Plus • ComTac™ • AM/FM • ProTac • CH-3 	<p>X-Series and Optime Earmuffs:</p> <p>X1A, PELTOR™ Over-the-Head X1B, PELTOR™ Neckband X1P3E, PELTOR™ Hard Hat-Attached X1P5E & X1P5E-OR Hard Hat-Attached X1P51E, PELTOR™ Hard Hat Attached, Wide Brim X2A, PELTOR™ Over-the-Head X2B, PELTOR™ Neckband X2P3E, PELTOR™ Hard Hat-Attached X2P5E Hard Hat-Attached H31A, PELTOR™ Hi-Viz Earmuffs H31P3E, PELTOR™ Hi-Viz Earmuffs M-985 PELTOR™ for Versaflo™ headgear H510A, PELTOR™ Optime I Over-the-head H510F, PELTOR™ Optime I Folding H510B, PELTOR™ Optime I Neckband H510P3E & P3GS, PELTOR™ Optime I Hard Hat Attached H520A, PELTOR™ Optime II Over-the-head H520F, PELTOR™ Optime II Folding H520FHV, PELTOR™ Optime II Folding H520B, PELTOR™ Optime II Neckband H520P3E & P3GS, PELTOR™ Optime II Hard Hat Attached H6B, PELTOR™ Optime 95 Neckband H6A, PELTOR™ Optime™ 95, Over-the-head H6P3E, PELTOR™ Optime™ 95, Hard Hat Attached H7A, PELTOR™ Optime™ 101, Other-the-head H7B, PELTOR™ Optime 101 Neckband H7P3E, PELTOR™ Optime™ 101, Hard Hat Attached H9A, PELTOR™ Optime™ 98, Over-the-head H9P3E, PELTOR™ Optime™ 98, Hard Hat Attached</p> <p>LiteCom Headsets:</p> <p>LiteCom FRS/BRS, Headband, MT53H7A4602-NA LiteCom FRS/BRS, Hard Hat Attach, MT53H7P3E4602-NA MT53H7A4600, PELTOR™ LiteCom BRS 2-way radio, Headband MT53H7P3E4600, PELTOR™ LiteCom BRS 2-way radio, Hard hat MT7H7A4610-NA, PELTOR™ LiteCom Plus, Headband MT7H7P3E4610-NA, PELTOR™ LiteCom Plus, Hard Hat Attached MT73H7A4D10, WS™ LiteCom PRO III Headset - Headband MT73H7B4D10, WS™ LiteCom PRO III Headset - Neckband MT73H7P3E4D10, WS™ LiteCom PRO III Headset - Hard Hat MT73H7F4D10NA-50, WS™ LiteCom PRO III Headset, IS - Headband MT73H7B4D10NA-50, WS™ LiteCom PRO III Headset, IS- Neckband MT73H7P3E4D10NA-50, WS™ LiteCom PRO III Headset, IS - Hard Hat WS™ LiteCom Plus, Headband, Foam Cushions MT73H7A4610WS6NA WS™ LiteCom Plus, Headband, GEL Cushions, MT73H7A4610WS6NA WS™ LiteCom Plus, Hard Hat Attach, Foam Cushions, MT73H7P3E4610WS6NA WS™ LiteCom Plus, Hard Hat Attach, GEL Cushions, MT73H7P3E4610WS6NA WS™ LiteCom Plus, Neckband, Foam Cushions, MT73H7B4610WS6NA WS™ LiteCom Plus, Neckband, GEL Cushions, MT73H7B4610WS6NA</p> <p>ComTac Headsets:</p> <p>MT20H682FB- Comtac XPI, Folding band, Foam Cushions MT20H682FB- Comtac XPI, Folding band, Gel Cushions MT20H682FB-N Comtac VI w/ NIB, Folding band, Foam Cushions AS-Patriot-92, ComTac V, Folding band, Foam cushions AS-Patriot-92, ComTac V, Folding band, Gel cushions MT20H682FB- ComTac™ V, Folding band, Foam cushions MT20H682FB- ComTac™ V, Folding band, Gel cushions MT20H682FB- ComTac™ VI w/NIB, Folding band, Foam Cushions MT20H682FB- ComTac™ VI, w/NIB, Folding band, Gel Cushions MT20H682BB- ComTac™ VI, Neckband, Foam Cushions MT20H682BB- ComTac™ VI, Neckband, Gel Cushions</p> <p>AM/FM Headsets:</p> <p>M2RX7A2-01, Alert™ FM Headband M2RX7P3E2-01, Alert™ FM Hard Hat Attached MRX21A2WS6, WS™ Alert™ XP, Headband MRX21P3E2WS6, WS™ Alert™ XP Hard Hat Attached M2RX21A3WS6 WS™ Alert™ XPI, Blue, Headband M2RX21A3WS6-AZ, WS™ Alert™ XPI, Yellow, Headband HRXS221A, WorkTunes™ Pro AM/FM, Headband HRXS221P3E, WorkTunes™ ProAM/FM, Hard Hat Attached</p> <p>ProTac Headsets:</p> <p>MT13H220A, ProTac™ III Slim Headsets, Headband MT13H220P3E, ProTac™ III Slim Headset, Hard Hat Attached MT13H221A, ProTac™ III Headset, Headband MT13H221P3E, ProTac™ III Headset, Hard Hat Attached MT15H7AWS6, WS™ PROTAC XPI, Headband, Foam or Gel MT15H7P3EWS6, WS™ PROTAC XPI, Hard Hat Attached, Foam or Gel MT15H7AWS6-111 WS™ PROTAC XPI, FLX2, Headband, Foam or Gel MT15H7P3EWS6-111 WS™ PROTAC XPI, FLX2, Hard Hat Attached, Foam or Gel</p> <p>CH-3**:</p> <p>CH-3 FLX2 Headset, Headband CH-3 FLX2 Headset, Neckband CH-3 FLX2 Headset, Hard Hat Attached</p>

3M Personal Safety Division

			CH-3 FLX2 Headset with PTT, Headband CH-3 FLX2 Headset with PTT, Neckband CH-3 FLX2 Headset with PTT, Hard Hat Attached CH-3 FLX2 Listen Only, Headband CH-3 FLX2 Listen Only, Neckband CH-3 FLX2 Listen Only, Hard Hat Attached
--	--	--	---

Probed Test Cushions	Probed Test Cushion SKU	Brand Names	Crossover Product SKUs and Descriptions
PELTOR™ Earmuffs X3 Test Cushions C	393-3003-2 	Earmuffs: <ul style="list-style-type: none"> • X3 	X3A, PELTOR™ Over-the-Head X3B, PELTOR™ Neckband ¹ X3P3E, PELTOR™ Hard Hat-Attached X3P5E Hard Hat-Attached
PELTOR™ Earmuffs X4/X5 Test Cushions D	393-3005-2 	Earmuffs: <ul style="list-style-type: none"> • X4, X5 Headsets: <ul style="list-style-type: none"> • CH-5 	X4A, PELTOR™ Over-the-Head X4B, PELTOR™ Neckband ¹ X4P3E, PELTOR™ Hard Hat-Attached X4P5E & X4P5E-OR, Hard Hat-Attached X4P51E, PELTOR™ Hard Hat Attached, Wide Brim X5A, PELTOR™ Over-the-Head X5B, PELTOR™ Neckband ¹ X5P3E, PELTOR™ Hard Hat-Attached X5P5E, Hard Hat-Attached CH-5, PELTOR™ High Attenuation Headset, Over-The-Head CH-5, PELTOR™ High Attenuation Headset, Hard Hat-Attached

Banded Hearing Protectors

Banded Hearing Protectors	Banded Hearing Protector sSKU	Brand Names	Crossover Product SKUs and Descriptions
EARcaps™ Model 200	393-2020-50 	Banded Hearing Protector: * E-A-R Caps™	321-2101, E-A-R Caps™ Model 200 Hearing Protector

NOTES:

1) E-A-Rfit™ can only be used to fit test the specific 3M hearing protectors listed in the Crossover Product column using the corresponding test probe. E-A-Rfit™ test results are not valid for any other 3M or non-3M hearing protectors.

2) If the earmuffs are worn in conjunction with a liftable visor, the visor should be in the up position when fit testing.

* The probed test cushions for X3B, X4B and X5B neckband earmuffs do not include the looped back plate, which is needed to attach the head strap for valid fit test results. The looped plate should be temporarily removed from the test subject's regular cushions and attached to the probed cushions as shown for fit testing with the headstrap.

** Remove gray back plate from the probed test cushion when fit testing all CH-3 headsets.



Personal Safety Division

3M Center, Building 235-2W-70
St. Paul, MN 55144-1000

3M PSD products are
occupational use only.

In United States of America

Technical Service: 1-800-243-4630
Customer Service: 1-800-328-1667
3M.com/workersafety

In Canada

Technical Service: 1-800-267-4414
Customer Service: 1-800-364-3577
3M.ca/Safety

© 3M 2022. All rights reserved.

3M, E-A-Rfit, the color yellow for earplugs and all other trademarks used herein are trademarks of 3M Company and affiliates. Used under license in Canada. All other trademarks are property of their respective owners. Please recycle.

